

# K4WA/C

## DECELERATION VALVE


### SERIES 10

#### THREADED PORTS

**p** max 150 bar

**Q** max 40 l/min


#### OPERATING PRINCIPLE




#### PERFORMANCES (measured with mineral oil of viscosity 36 cSt at 50°C)

Maximum operating pressure	bar	150
Cracking pressure of the check valve	bar	0,5
Maximum flow rate	l/min	40
Needed force on the lever to operate:		
- at beginning	Kg	6,8
- at end stroke		12,0
Maximum leakage with closed valve (Δp 100 bar)	l/min	0,05
Stroke (from all open to completely closed)	mm	20
Ambient temperature range	°C	-20 / +50
Fluid temperature range	°C	-20 / +80
Fluid viscosity range	cSt	10 + 400
Fluid contamination degree	According to ISO 4406:1999 class 20/18/15	
Recommended viscosity	cSt	25
Mass	kg	2,5



#### HYDRAULIC SYMBOL



### 1 - IDENTIFICATION CODE



### 2 - CHARACTERISTIC CURVES (values obtained with viscosity of 36 cSt at 50°C)



**NOTE:** For flow A→P, with valve closed, add the cracking pressure (0,5 bar) to the values shown in the diagram.

### 3 - HYDRAULIC FLUIDS

Use mineral oil-based hydraulic fluids HL or HM type, according to ISO 6743-4. For these fluids, use NBR seals. For fluids HFDR type (phosphate esters) use FPM seals (code V). For the use of other kinds of fluid such as HFA, HFB, HFC, please consult our technical department. Using fluids at temperatures higher than 80 °C causes a faster degradation of the fluid and of the seals characteristics. The fluid must be preserved in its physical and chemical characteristics.

### 4 - OVERALL AND MOUNTING DIMENSIONS

